





4802 SLOPE REDUCER

SLOPE REDUCER









Details


Reinforced inner part, tested one by one

- Place the reducer along the drinking line (usually in the middle). For high slopes, maybe that more that one reducer is needed along a single drinking line.
- The first transparent hose shows the water pressure in the middle of the line, where the reducer is positioned. If the water supply regulator has been placed at the beginning of the line, this water level will be higher than the one shown at the beginning of the line.
- By actioning the handle below the slope reducer (the same as for the water supply regulator), you will modify the water pressure starting from the point where the slope reducer is positioned. The water pressure will be modified as shown by the water level in the second transparent hose. After that, you must check the water pressure at the end of the drinking line.

Using our slope reducer 4802, all the negative effects of a slope can be reduced, by making an effective separation in two or more parts of one single drinking line, so that each part is independently adjustable. **We advise to put one slope reducer 4802 in-line each 15 cm of slope.**



To clean the line by flushing, a bypass (art. 4858).



Pos.	SE	Q.tà	Codice	Descrizione
1		1	4706I	Dado E Pg-UNI5588 M8-INOX
2		1	4726	Molla D3-De20.1-L650-P21
3		1	4727	Sfera D 6,65 galleg.x Finelinea
4		1	4728	Tubo Cristal flex 9x12x900
5		2	473303	Anello OR 3106 (d2,62xD26,64)
6		1	4781	As.Rubinet.Sfera 3/4" Reggi Tubo Cristal
7		1	478405	Anello OR d3x21
8		1	480202AK	As.Guscio Superiore LL Foro Laterale
9		1	480104	Anello OR 123 (d2.62-D17.86)
10		2	480105	Vite TCCR-AF 5.5x19-DIN-7981C
11		1	480107	Guarnizione D15.8-L4.5 tenuta regolatore
12		1	480111	Vite sping.regolatore
13		1	480112	Membrana in gomma
14		1	480113	Disco spingi menbrana
15		1	480114	Guscio Inferiore x riduttore
16		1	480115	Molla C-D3-De40-L45-P13.5
17		12	480116	Vite TCCR-AF 4.2x13-DIN-7981C
18		1	480117	Vite regol.regolatore
19		1	480119	Spina Cil.UNI1707-D3x30-INOX
20		1	480150	Kit Particolari interni Reg.Press.
21		1	4826	Supporto sost.tubo Cristal su corda
22		1	4849	As. Valvola Sfiato Tubo Cristal Flex
23		1	480203	Ugello D.10 x regol.Pendenz.LAT
24		1	480205	Tappo Laterale Chiudi Condotto